


Extension- and compensating cables, single-paired

PVC, silicone, FEP or glass fibre insulated



Info

- Available in many different designs
- New: Thermocouple cables type K



Norm references / approvals

- Space-saving and flexible
- For more detailed information, see appendix T8 and data sheets

Application range

- Allows temperature measurement even in places where non-contact temperature measurement is not possible or expedient
- In combination with a sheath thermocouple in the area of temperature measurement or production process control. The insulation material should be selected with reference to the maximum ambient temperature at the connection head of the thermocouple.
- **Conductor materials (alloys): Fe/CuNi (LX, JX)**
Conductor alloys are identical to thermocouple alloys
- **NiCr/Ni (K, KX, KCA)**
K and KX version - conductor alloys are identical to thermocouple alloys
KCA version: Compensating alloys (for KCA: Fe/CuNi), not identical to thermocouple alloys
- **PtRh/Pt (RCB, SCB)**
Compensating alloys (for RCB, SCB: Cu/CuNi) are not identical to thermocouple alloys

Norm references / approvals

- **Colour code DIN 43710**
Negative conductor and outer sheath:
Fe/CuNi: blue
NiCr/Ni: green
PtRh/Pt: white
Positive conductor: always rot
- **IEC 60 584**
Positive conductor and sheath:
Fe/CuNi: black
NiCr/Ni: green
PtRh/Pt: orange
Negative conductor: always white

Design

- **Design abbreviations:**PVC: polyvinylchloride
SIL: silicone rubber
GL: glass silk
FEP: fluorinated ethylene propylene
EGL: E-glass
C: Copper braiding
ST: aluminium foil shield
S: Steel wire braiding
- **Design example PVC-PVC-S-PVC:**
- PVC core insulation
- PVC inner sheath
- Steel wire braiding
- PVC outer sheath
- **Examples shown (top to bottom):**
Fe/CuNi DIN 2x1.5 PVC
NiCr/Ni IEC 2x1.5 GL-GL
PtRh/Pt IEC 2x1.5 GL-GL-S
NiCr/Ni DIN 2x1.5 SIL-GL
NiCr/Ni DIN 2x1.5 PVC-PVC
PtRh/Pt DIN 2x1.5 SIL-SIL
Fe/CuNi IEC 2x1.5 SIL-SIL-S
NiCr/Ni IEC 2x1.5 SIL
PtRh/Pt IEC 2x1.5 SIL-GL-S
Fe/CuNi IEC 2x0.22 PVC-PVC-C-PVC
NiCr/Ni IEC 2x1.5 PVC-ST-PVC
Fe/CuNi DIN 2x1.5 PVC-PVC-S-PVC

Technical data

Classification
ETIM 5.0 Class-ID: EC000838
ETIM 5.0 Class-Description: Thermo-compensation cable

Based on
Limit deviation in accordance with DIN and IEC in accordance with class 2

Conductor design
1.5 mm²: approx. 48 x 0.20 mm
0.75 mm²: approx. 24 x 0.20 mm
0.5 mm²: approx. 16 x 0.20 mm
0.22 mm²: approx. 7 x 0.20 mm

Minimum bending radius
Without metal braiding:
12 x cable diameter
with metal braiding:
15 x cable diameter

Temperature range
(referring to insulation and sheath materials)
PVC: -5°C to +80°C
Silicone: -25°C to +180°C
Glass fibre: -25°C to +200°C
FEP: -100°C to +205°C
E-glass: -25°C to +400°C

Article number	Reference/ article designation	Thermocouple	Design	Cable design	Number of cores and mm ² per conductor	Outer diameter [mm]	Outer dimensions, width x height (mm)	Weight (kg/ km)
0.22 mm² extension and compensating cables								
0151051	KE 9-022 L	Fe/CuNi	DIN LX	PVC-PVC	2 x 0.22	4.0		22
0161051	KE 9-022 L	Fe/CuNi	IEC JX	PVC-PVC	2 x 0.22	4.0		22
0152051	KN 9-022 L	NiCr/Ni	DIN KCA	PVC-PVC	2 x 0.22	4.0		22
0162051	KN 9-022 L	NiCr/Ni	IEC KCA	PVC-PVC	2 x 0.22	4.0		22
0153051	KP 9-022 L	PtRh/Pt	DIN RCB, SCB	PVC-PVC	2 x 0.22	4.0		22
0163051	KP 9-022 L	PtRh/Pt	IEC RCB, SCB	PVC-PVC	2 x 0.22	4.0		22
0151052	KE 5-022 L-CY	Fe/CuNi	DIN LX	PVC-PVC-C-PVC	2 x 0.22	4.9		31
0161052	KE 5-022 L-CY	Fe/CuNi	IEC JX	PVC-PVC-C-PVC	2 x 0.22	4.9		31
0152052	KN 5-022 L-CY	NiCr/Ni	DIN KCA	PVC-PVC-C-PVC	2 x 0.22	4.9		31
0162052	KN 5-022 L-CY	NiCr/Ni	IEC KCA	PVC-PVC-C-PVC	2 x 0.22	4.9		31
0153052	KP 5-022 L-CY	PtRh/Pt	DIN RCB, SCB	PVC-PVC-C-PVC	2 x 0.22	4.9		31
0163052	KP 5-022 L-CY	PtRh/Pt	IEC RCB, SCB	PVC-PVC-C-PVC	2 x 0.22	4.9		31
1161011	KN FEP-SIL	NiCr/Ni	IEC KCA	FEP-SIL	2 x 0.22	3,8		22
1161007	K FEP-C-FEP	NiCr/Ni	IEC K	FEP-C-FEP	2 x 0.22	3.0		22
Thermocouple cables type K, 0.5 mm								
1161008	K FEP-FEP	NiCr/Ni	IEC K	FEP-FEP oválný	2 x 0.5		2.4 x 1.5	45
1161009	K GL-GL	NiCr/Ni	IEC K	EGL-EGL oválný	2 x 0.5		2.3 x 1.3	45
0.5 mm² extension and compensating cables								
0151030	KE 91 L	Fe/CuNi	DIN LX	PVC-PVC	2 x 0.5	5.4		45
0161030	KE 91 L	Fe/CuNi	IEC JX	PVC-PVC	2 x 0.5	5.4		45
0152040	KN 91 L	NiCr/Ni	DIN KCA	PVC-PVC	2 x 0.5	5.4		45
0162040	KN 91 L	NiCr/Ni	IEC KCA	PVC-PVC	2 x 0.5	5.4		45
0151040	KE 41 L-SIL	Fe/CuNi	DIN LX	SIL-SIL-S oval	2 x 0.5		6.4 x 4.4	51
0161040	KE 41 L-SIL	Fe/CuNi	IEC JX	SIL-SIL-S oval	2 x 0.5		6.4 x 4.4	51
0152030	KN 41 L-SIL	NiCr/Ni	DIN KCA	SIL-SIL-S oval	2 x 0.5		6.4 x 4.4	51
0162030	KN 41 L-SIL	NiCr/Ni	IEC KCA	SIL-SIL-S oval	2 x 0.5		6.4 x 4.4	51
0.75 mm² extension and compensating cables								
0151035	KE 92 L	Fe/CuNi	DIN LX	PVC-PVC	2 x 0.75	6.0		56
0161035	KE 92 L	Fe/CuNi	IEC JX	PVC-PVC	2 x 0.75	6.0		56
0152045	KN 92 L	NiCr/Ni	DIN KCA	PVC-PVC	2 x 0.75	6.0		56
0162045	KN 92 L	NiCr/Ni	IEC KCA	PVC-PVC	2 x 0.75	6.0		56
0151050	KE 42 L-SIL	Fe/CuNi	DIN LX	SIL-SIL-S oval	2 x 0.75		6.4 x 4.4	58
0161050	KE 42 L-SIL	Fe/CuNi	IEC JX	SIL-SIL-S oval	2 x 0.75		6.4 x 4.4	58
0152035	KN 42 L-SIL	NiCr/Ni	DIN KCA	SIL-SIL-S oval	2 x 0.75		6.4 x 4.4	58
0162035	KN 42 L-SIL	NiCr/Ni	IEC KCA	SIL-SIL-S oval	2 x 0.75		6.4 x 4.4	58

PVC-insulated versions 1.5 mm²

Article number	Reference/ article designation	Thermocouple	Design	Cable design	Number of cores and mm ² per conductor	Outer diameter [mm]	Outer dimensions, width x height (mm)	Weight (kg/ km)
0151001	KE 1 L	Fe/CuNi	DIN LX	PVC	2 x 1.5	5.4		40
0161001	KE 1 L	Fe/CuNi	IEC JX	PVC	2 x 1.5	5.4		40
0152001	KN 1 L	NiCr/Ni	DIN KCA	PVC	2 x 1.5	5.4		40
0162001	KN 1 L	NiCr/Ni	IEC KCA	PVC	2 x 1.5	5.4		40
0151010	KE 9 L	Fe/CuNi	DIN LX	PVC-PVC round	2 x 1.5	7.1		79
0161010	KE 9 L	Fe/CuNi	IEC JX	PVC-PVC round	2 x 1.5	7.1		79
0152010	KN 9 L	NiCr/Ni	DIN KCA	PVC-PVC round	2 x 1.5	7.1		79
0162010	KN 9 L	NiCr/Ni	IEC KCA	PVC-PVC round	2 x 1.5	7.1		79
0154010	KXN 9 L	NiCr/Ni	DIN KX	PVC-PVC round	2 x 1.5	7.1		79
0164010	KXN 9 L	NiCr/Ni	IEC KX	PVC-PVC round	2 x 1.5	7.1		79
0153010	KP 9 L	PtRh/Pt	DIN RCB, SCB	PVC-PVC round	2 x 1.5	7.1		79
0163010	KP 9 L	PtRh/Pt	IEC RCB, SCB	PVC-PVC round	2 x 1.5	7.1		79
0151017	KE 12 L	Fe/CuNi	DIN LX	PVC-PVC oval	2 x 1.5		7.2 x 4.4	69
0161017	KE 12 L	Fe/CuNi	IEC JX	PVC-PVC oval	2 x 1.5		7.2 x 4.4	69
0152017	KN 12 L	NiCr/Ni	DIN KCA	PVC-PVC oval	2 x 1.5		7.2 x 4.4	69
0162017	KN 12 L	NiCr/Ni	IEC KCA	PVC-PVC oval	2 x 1.5		7.2 x 4.4	69
0154011	KE 20 L	Fe/CuNi	DIN LX	PVC-ST-PVC	2 x 1.5	7.6		85
0164011	KE 20 L	Fe/CuNi	IEC JX	PVC-ST-PVC	2 x 1.5	7.6		85
0154012	KN 20 L	NiCr/Ni	DIN KCA	PVC-ST-PVC	2 x 1.5	7.6		85
0164012	KN 20 L	NiCr/Ni	IEC KCA	PVC-ST-PVC	2 x 1.5	7.6		85
0154013	KXN 20 L	NiCr/Ni	DIN KX	PVC-ST-PVC	2 x 1.5	7.6		85
0164013	KXN 20 L	NiCr/Ni	IEC KX	PVC-ST-PVC	2 x 1.5	7.6		85
0154014	KP 20 L	PtRh/Pt	DIN RCB, SCB	PVC-ST-PVC	2 x 1.5	7.6		85
0164014	KP 20 L	PtRh/Pt	IEC RCB, SCB	PVC-ST-PVC	2 x 1.5	7.6		85
0151011	KE 9 L-S	Fe/CuNi	DIN LX	PVC-PVC-S	2 x 1.5	8.0		140
0161011	KE 9 L-S	Fe/CuNi	IEC JX	PVC-PVC-S	2 x 1.5	8.0		140
0152011	KN 9 L-S	NiCr/Ni	DIN KCA	PVC-PVC-S	2 x 1.5	8.0		140
0162011	KN 9 L-S	NiCr/Ni	IEC KCA	PVC-PVC-S	2 x 1.5	8.0		140
0157514	KE 9 L-SY	Fe/CuNi	DIN LX	PVC-PVC-S-PVC	2 x 1.5	10.3		160
0167514	KE 9 L-SY	Fe/CuNi	IEC JX	PVC-PVC-S-PVC	2 x 1.5	10.3		160
0157513	KN 9 L-SY	NiCr/Ni	DIN KCA	PVC-PVC-S-PVC	2 x 1.5	10.3		160
0167513	KN 9 L-SY	NiCr/Ni	IEC KCA	PVC-PVC-S-PVC	2 x 1.5	10.3		160
0157515	KP 9 L-SY	PtRh/Pt	DIN RCB, SCB	PVC-PVC-S-PVC	2 x 1.5	10.3		160
0167515	KP 9 L-SY	PtRh/Pt	IEC RCB, SCB	PVC-PVC-S-PVC	2 x 1.5	10.3		160
Silicone-insulated versions 1.5 mm²								
0151003	KE 1 L-SIL	Fe/CuNi	DIN LX	SIL	2 x 1.5	5.4		40
0161003	KE 1 L-SIL	Fe/CuNi	IEC JX	SIL	2 x 1.5	5.4		40
0152003	KN 1 L-SIL	NiCr/Ni	DIN KCA	SIL	2 x 1.5	5.4		40
0162003	KN 1 L-SIL	NiCr/Ni	IEC KCA	SIL	2 x 1.5	5.4		40
0151022	KE 15 L-SIL	Fe/CuNi	DIN LX	SIL-SIL round	2 x 1.5	7.0		76
0161022	KE 15 L-SIL	Fe/CuNi	IEC JX	SIL-SIL round	2 x 1.5	7.0		76
0152022	KN 15 L-SIL	NiCr/Ni	DIN KCA	SIL-SIL round	2 x 1.5	7.0		76
0162022	KN 15 L-SIL	NiCr/Ni	IEC KCA	SIL-SIL round	2 x 1.5	7.0		76
0153022	KP 15 L-SIL	PtRh/Pt	DIN RCB, SCB	SIL-SIL round	2 x 1.5	7.0		76
0163022	KP 15 L-SIL	PtRh/Pt	IEC RCB, SCB	SIL-SIL round	2 x 1.5	7.0		76
0151023	KE 15 L-SIL-S	Fe/CuNi	DIN LX	SIL-SIL-S round	2 x 1.5	7.8		105
0161023	KE 15 L-SIL-S	Fe/CuNi	IEC JX	SIL-SIL-S round	2 x 1.5	7.8		105
0152023	KN 15 L-SIL-S	NiCr/Ni	DIN KCA	SIL-SIL-S round	2 x 1.5	7.8		105
0162023	KN 15 L-SIL-S	NiCr/Ni	IEC KCA	SIL-SIL-S round	2 x 1.5	7.8		105
0153023	KP 15 L-SIL-S	PtRh/Pt	DIN RCB, SCB	SIL-SIL-S round	2 x 1.5	7.8		105
0163023	KP 15 L-SIL-S	PtRh/Pt	IEC RCB, SCB	SIL-SIL-S round	2 x 1.5	7.8		105
0151007	KE 4 L-SIL-S	Fe/CuNi	DIN LX	SIL-SIL-S oval	2 x 1.5		8.0 x 5.2	85
0161007	KE 4 L-SIL-S	Fe/CuNi	IEC JX	SIL-SIL-S oval	2 x 1.5		8.0 x 5.2	85
0152007	KN 4 L-SIL-S	NiCr/Ni	DIN KCA	SIL-SIL-S oval	2 x 1.5		8.0 x 5.2	85
0162007	KN 4 L-SIL-S	NiCr/Ni	IEC KCA	SIL-SIL-S oval	2 x 1.5		8.0 x 5.2	85
0153007	KP 4 L-SIL-S	PtRh/Pt	DIN RCB, SCB	SIL-SIL-S oval	2 x 1.5		8.0 x 5.2	85
0163007	KP 4 L-SIL-S	PtRh/Pt	IEC RCB, SCB	SIL-SIL-S oval	2 x 1.5		8.0 x 5.2	85
0151019	KE 13 L-SIL	Fe/CuNi	DIN LX	SIL-GL oval	2 x 1.5		6.0 x 3.3	50
0161019	KE 13 L-SIL	Fe/CuNi	IEC JX	SIL-GL oval	2 x 1.5		6.0 x 3.3	50
0152019	KN 13 L-SIL	NiCr/Ni	DIN KCA	SIL-GL oval	2 x 1.5		6.0 x 3.3	50
0162019	KN 13 L-SIL	NiCr/Ni	IEC KCA	SIL-GL oval	2 x 1.5		6.0 x 3.3	50
0153019	KP 13 L-SIL	PtRh/Pt	DIN RCB, SCB	SIL-GL oval	2 x 1.5		6.0 x 3.3	50
0151015	KE 11 L-SIL-S	Fe/CuNi	DIN LX	SIL-GL-S	2 x 1.5	6.7		82
0161015	KE 11 L-SIL-S	Fe/CuNi	IEC JX	SIL-GL-S	2 x 1.5	6.7		82
0152015	KN 11 L-SIL-S	NiCr/Ni	DIN KCA	SIL-GL-S	2 x 1.5	6.7		82
0162015	KN 11 L-SIL-S	NiCr/Ni	IEC KCA	SIL-GL-S	2 x 1.5	6.7		82
0153015	KP 11 L-SIL-S	PtRh/Pt	DIN RCB, SCB	SIL-GL-S	2 x 1.5	6.7		82
0163015	KP 11 L-SIL-S	PtRh/Pt	IEC RCB, SCB	SIL-GL-S	2 x 1.5	6.7		82
1161012	KP 11 L-SIL-S	NiCr/Ni	IEC KCA	SIL-GL-S oválny	2 x 1.5		6.8 x 4.1	82
Glass fibre-insulated versions 1.5 mm²								
0151005	KE 3 L	Fe/CuNi	DIN LX	GL-GL oval	2 x 1.5		5.1 x 2.7	64
0161005	KE 3 L	Fe/CuNi	IEC JX	GL-GL oval	2 x 1.5		5.1 x 2.7	64
0152005	KN 3 L	NiCr/Ni	DIN KCA	GL-GL oval	2 x 1.5		5.1 x 2.7	64
0162005	KN 3 L	NiCr/Ni	IEC KCA	GL-GL oval	2 x 1.5		5.1 x 2.7	64
0153005	KP 3 L	PtRh/Pt	DIN RCB, SCB	GL-GL oval	2 x 1.5		5.1 x 2.7	64
0163005	KP 3 L	PtRh/Pt	IEC RCB, SCB	GL-GL oval	2 x 1.5		5.1 x 2.7	64
0151006	KE 4 L-S	Fe/CuNi	DIN LX	GL-GL-S oval	2 x 1.5		5.9 x 3.7	87
0161006	KE 4 L-S	Fe/CuNi	IEC JX	GL-GL-S oval	2 x 1.5		5.9 x 3.7	87
0152006	KN 4 L-S	NiCr/Ni	DIN KCA	GL-GL-S oval	2 x 1.5		5.9 x 3.7	87
0162006	KN 4 L-S	NiCr/Ni	IEC KCA	GL-GL-S oval	2 x 1.5		5.9 x 3.7	87
0153006	KP 4 L-S	PtRh/Pt	DIN RCB, SCB	GL-GL-S oval	2 x 1.5		5.9 x 3.7	87
0163006	KP 4 L-S	PtRh/Pt	IEC RCB, SCB	GL-GL-S oval	2 x 1.5		5.9 x 3.7	87

Unless otherwise specified, the product values shown are nominal values. You can receive further values, such as tolerances, upon request if they are available and have been released for publication.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging: Ring ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred packaging (e.g. 1 x 500 m drum or 5 x 100 m rings)

Photographs are not to scale and do not represent detailed images of the respective products.